


A Safer Turnkey Solution for Aseptic Environments

Advanced microfiber construction with super-fine microfiber filaments effectively removes particles to help ensure a cleaner and safer environment. A 70/30 IPA blend offers the perfect saturation level while our robust sterilization process offers absolute confidence.

Features and Benefits

- Removes 99.9% of particles down to .1 micron in size⁴
- 70% isopropyl alcohol (IPA), 30% USP-grade DI water
- 10⁻⁶ Sterility Assurance Level (SAL)
- Superior durability and resistance to tearing
- High absorbency and coverage for enhanced worker efficiency
- Extremely fine filament design increases surface contact for improved cleaning performance
- Certificate of Sterility included

STERILE PRESATURATED NONWOVEN MICROFIBER CLEANROOM WIPES



Item	Size	Quantity
WA209S	9" x 9" (23 cm x 23 cm)	30 wipes/bag • 27 bags/case
WA212S	12" x 12" (30 cm x 30 cm)	30 wipes/bag • 12 bags/case



Visionary Cleaning System

Saturix is a complete system for critical cleaning featuring innovative carts, mops and wipes backed by 100 years of cleaning experience. With focused product selection, it's easy to find exactly what you need right now.

To learn more about our products, visit us online at Saturix.com or contact us at **+1 (413) 598-8344** or info@saturix.com



Sterile Presaturated Nonwoven Microfiber Wipes

Rigorously tested according to IEST-RP-CC004.3 standards

Cleanroom Level Recommendation*

ISO 3 4 5 6 7 8

Property	Typical Value
Basis Weight	1.3 oz/yd ² 44 g/m ²
Thickness	12 mils 0.30 mm
Sorbency Capacity	Intrinsic - 7 mL/g Extrinsic - 295 mL/m ²
Nonvolatile Residue (NVR)	Deionized Water - 0.018 mg/g Isopropyl Alcohol - 0.034 mg/g
Ions	Sodium - 102 ppm Chloride - 78 ppm
Particles	0.5 - 5.0 μm - 93 million/m ² 5.0 - 10.0 μm - 1.4 million/m ²
Fibers	> 100 μm - 17,500 fibers/m ²

Notes

1. Data shown are typical values and should not be used as product specifications.
2. Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions. Current and/or comparison data may be available. Please contact an FG Clean Wipes representative for details.
3. FG Clean Wipes makes general recommendations on which wipes are suitable for different cleanroom classifications. However, specific applications may affect that recommendation. The final decision should be made by the end user for their particular application.
4. Based on third party testing.

* Cleanroom class recommendations are based on typical industry-wide applications and general cleanliness classifications. Please consult our experienced FG Clean Wipes sales representatives for specific cleanroom selections for critical and/or specialized applications based on a wider selection of criteria.

To learn more about our products, visit us online at Saturix.com or contact us at **+1 (413) 598-8344** or info@saturix.com

