


STERILE  
POLYESTER KNIT  
WITH BORDER SEAL

Insurance for Purity,  
Cleanliness and  
Aseptic Safety

These sterile, ultra-pure knit polyester wipes feature a contiguous sealed border to reduce fibers and particulates when shedding is a concern and cleanliness is critical.



## Features and Benefits

- Sealed borders increase cleanliness and abrasion resistance
- 10<sup>-6</sup> sterility assurance level (SAL)
- Ultra-low extractables, ions, and NVRs for critical tasks
- High chemical compatibility for use with a variety of solvents
- Cleanliness and dependability for ISO Class 3 usage
- Lot-traceable sterility for aseptic usage

Cleanroom Level Recommendation\*



Item	Size	Quantity
WDB409S	9" x 9" (23 cm x 23 cm)	25 wipes/bag • 6 bags/pack • 10 packs/case
WDB412S	12" x 12" (30 cm x 30 cm)	25 wipes/bag • 6 bags/pack • 6 packs/case



### Visionary Cleaning System

Saturix is a complete system for critical cleaning featuring innovative carts, mops and wipes backed by 100 years of cleaning experience. With focused product selection, it's easy to find exactly what you need right now.

To learn more about our products, visit us online at [Saturix.com](http://Saturix.com) or contact us at +1 (413) 598-8344 or [info@saturix.com](mailto:info@saturix.com)



**Sterile Polyester Knit with Border Seal**

Rigorously tested according to IEST-RP-CC004.3 standards

Cleanroom Level Recommendation\*

ISO **3** **4** **5** **6** **7** **8**

Property	Typical Value
<b>Basis Weight</b>	4.0 oz/yd <sup>2</sup>   136 g/m <sup>2</sup>
<b>Thickness</b>	20 mils   0.51 mm
<b>Sorbency Capacity</b>	<b>Intrinsic</b> - 3 mL/g <b>Extrinsic</b> - 366 mL/m <sup>2</sup>
<b>Nonvolatile Residue (NVR)</b>	<b>Deionized Water</b> - 0.011 mg/g <b>Isopropyl Alcohol</b> - 0.029 mg/g
<b>Ions</b>	<b>Sodium</b> - < 0.8 ppm <b>Chloride</b> - 0.2 ppm
<b>Particles</b>	<b>0.5 - 5.0 µm</b> - 10.6 million/m <sup>2</sup> <b>5.0 - 10.0 µm</b> - 0.714 million/m <sup>2</sup>
<b>Fibers</b>	<b>&gt; 100 µm</b> - 295 fibers/m <sup>2</sup>

**Notes**

1. Data shown are typical values and should not be used as product specifications.
2. Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions. Current and/or comparison data may be available. Please contact an FG Clean Wipes representative for details.
3. FG Clean Wipes makes general recommendations on which wipes are suitable for different cleanroom classifications. However, specific applications may affect that recommendation. The final decision should be made by the end user for their particular application.

\* Cleanroom class recommendations are based on typical industry-wide applications and general cleanliness classifications. Please consult our experienced FG Clean Wipes sales representatives for specific cleanroom selections for critical and/or specialized applications based on a wider selection of criteria.

To learn more about our products, visit us online at [Saturix.com](https://www.saturix.com) or contact us at **+1 (413) 598-8344** or [info@saturix.com](mailto:info@saturix.com).

